

DynaWash Duo

For laboratories performing a high volume of repeated wash tests,
DynaWash Duo with integrated spinner will provide a life time of laundering in a fraction of the time.

Now with the James Heal touchscreen user interface, the most simple to use controller for textile testing.





DynaWash Duo

GARMENT & PRINTED FABRIC DURABILITY TESTER

DynaWash Duo simulates the lifetime of laundering in one wash. The new integrated spinner reduces the hassle of rinsing and extracting excess water in a separate machine.













KEY BENEFITS

A LIFETIME OF LAUNDERING

Fifteen minutes of testing in the DynaWash is approximately equivalent to five domestic washes, removing the need for repeated wash and dry tests.

This results in reduced cost, labour and required laboratory space and an increased capacity for testing.

INTEGRATED SPINNER

An integrated spinner with a safety interlocked lid allows the user to rinse and extract excess water from samples without having to move them across the laboratory to a different instrument.

The spinner, which has an automatic drain function, is mounted on springs to minimise noise and movement. The spin time is displayed on the user interface, but is controlled by a separate button for ease of use.

TOUCHSCREEN USER INTERFACE

An intuitive touchscreen user interface, designed alongside textile technicians in a working laboratory, offers testing which is simple to set up with intuitive temperature and time controls.

MULTIPLE TESTS

Multiple tests can be performed in this one instrument, including print durability, pleat retention, cockling, flock retention, crinkling, differential shrinkage, security of attachments and more.

APPROVED BY M&S

Both the DynaWash and DynaWash Duo are approved by Marks & Spencer.

QUALITY COMPONENTS

The process bath and impeller are constructed in stainless steel for improved quality and a longer lifespan. The robust design and build results in reduced downtime in comparison to domestic appliances.

SAFETY & RELIABILITY

A range of safety features include an IP rated touchscreen, interlock to automatically stop the impeller when the lid is open and a heating element safety cut out.

A RANGE OF STANDARDS

DynaWash complies with a range of standards, including retailer test methods such as M&S, Next and the Arcadia Group.

Dimensions (mm)Height (mm)Width (mm)Depth (mm)Weight (kg)DynaWash Duo12401010759136.0

CONTACT US

For more information

web: www.james-heal.co.uk/en/dynawash

tel: +44 (0) 1422 366 355 email: sales@james-heal.co.uk

